

## PRODUCTOVERZICHT



# pritti® multidisc ZrO<sub>2</sub>

Suitable for all conventional open milling machines with adapter for **blank diameter 98.5 mm.**

**pritti® multidisc ZrO<sub>2</sub> – High Translucent** with a **translucency of 49 %**, Sintering temperature 1,450° C  
Flexural strength > **650 MPa** - Highest Aesthetics - Released for bridges up to 3 units

HIGH TRANSLUCENT	SHADES	HEIGHTS IN MM
white	white	10, 12, 14, 16, 18, 20, 25
monochrome in 16 VITA® classical shades	A1, A2, A3, A3,5, A4, B1, B2, B3, B4, C1, C2, C3, C4, D2, D3, D4	10, 12, 14, 16, 18, 20, 25
multicolor	A light (shade range: A1-A3), A dark (shade range: A3,5-A4), B light (shade range: B1-B2), B dark (shade range: B3-B4), C light (shade range: C1-C2), C dark (shade range: C3-C4), D light (shade range: D2-D4), priti® bleach (shade range: 0M1, 0M2, 0M3, 1M1)	14, 18, 20, 25

**pritti® multidisc ZrO<sub>2</sub> – Extra Translucent** with a **translucency of 45 %**, Sintering temperature 1,450° C  
Flexural strength > **1.150 MPa** - Very High Aesthetics, Released for bridges up to 16 units

EXTRA TRANSLUCENT	SHADES	HEIGHTS IN MM
white	white	10, 12, 14, 16, 18, 20, 25
multicolor	A light (shade range: A1-A3), A dark (shade range: A3,5-A4), B light (shade range: B1-B2), B dark (shade range: B3-B4), C light (shade range: C1-C2), C dark (shade range: C3-C4), D light (shade range: D2-D4), priti® bleach (shade range: 0M1, 0M2, 0M3, 1M1)	14, 18, 20, 25

**pritti® multidisc ZrO<sub>2</sub> – Translucent** with a **translucency of 40 %**, Sintering temperature 1,450° C  
Flexural strength > **1,150 MPa** - High Aesthetics - Released for bridges up to 16 units

TRANSLUCENT	SHADES	HEIGHTS IN MM
white	white	10, 12, 14, 16, 18, 20, 25
monochrome in 16 VITA® classical shades	A1, A2, A3, A3,5, A4, B1, B2, B3, B4, C1, C2, C3, C4, D2, D3, D4	10, 12, 14, 16, 18, 20, 25
multicolor	A light (shade range: A1-A3), A dark (shade range: A3,5-A4), B light (shade range: B1-B2), B dark (shade range: B3-B4), C light (shade range: C1-C2), C dark (shade range: C3-C4), D light (shade range: D2-D4)	14, 18, 20, 25











**pritti® multidisc ZrO<sub>2</sub> – Opaque** with a **translucency of 35 %**, Sintering temperature 1,450° C  
Flexural strength > **1,150 MPa** - Released for bridges up to 16 units

OPAQUE	SHADES	HEIGHTS IN MM
white	white	10, 12, 14, 16, 18, 20, 25
monochrome in 16 VITA® classical shades	A1, A2, A3, A3,5, A4, B1, B2, B3, B4, C1, C2, C3, C4, D2, D3, D4	10, 12, 14, 16, 18, 20, 25

TRANSLUCENCY

**MADE IN GERMANY**

After Added Value

	Opaque	Translucent	Extra Translucent	High Translucent
multicolor		 <p>pri<sup>ti</sup>®multidisc ZrO<sub>2</sub> multicolor Translucent</p>	 <p>pri<sup>ti</sup>®multidisc ZrO<sub>2</sub> multicolor Extra Translucent</p>	 <p>pri<sup>ti</sup>®multidisc ZrO<sub>2</sub> multicolor High Translucent</p>
monochromatic	 <p>pri<sup>ti</sup>®multidisc ZrO<sub>2</sub> 16 VITA® shades A1 - D4 Opaque</p>	 <p>pri<sup>ti</sup>®multidisc ZrO<sub>2</sub> 16 VITA® Shades A1 - D4 Translucent</p>		 <p>pri<sup>ti</sup>®multidisc ZrO<sub>2</sub> 16 VITA® Shades A1 - D4 High Translucent</p>
white	 <p>pri<sup>ti</sup>®multidisc ZrO<sub>2</sub> white Opaque</p>	 <p>pri<sup>ti</sup>®multidisc ZrO<sub>2</sub> white Translucent</p>	 <p>pri<sup>ti</sup>®multidisc ZrO<sub>2</sub> white Extra Translucent</p>	 <p>pri<sup>ti</sup>®multidisc ZrO<sub>2</sub> white High Translucent</p>

After Aesthetics

ADDED VALUE & AESTHETICS

## multicolor

### High Translucent

49 % translucency  
flexural strength > 650 MPa  
bridges with up to 3 units

#### multicolor



#### Variants multicolor

4 light variations  
3 dark variations  
1 bleach shade

### Extra Translucent

45 % translucency  
flexural strength > 1,150 MPa  
suitable for a wide range of indications

#### multicolor



#### Variants multicolor

4 light variations  
3 dark variations  
1 bleach shade

### Translucent

40 % translucency  
flexural strength > 1,150 MPa  
suitable for a wide range of indications

#### multicolor



#### Variants multicolor


4 light variations  
3 dark variations

## monochromatic

### High Translucent

49 % translucency  
flexural strength > 650 MPa  
suitable for a wide range of indications

16 VITA® shades and white



Variants  
monochromatic  
16 VITA® shades

Variants  
white

### Extra Translucent

45 % translucency  
flexural strength > 1,150 MPa  
suitable for a wide range of indications

white




Variants  
white

### Translucent

40 % translucency  
flexural strength > 1,150 MPa  
suitable for a wide range of indications

16 VITA® shades and white




Variants  
monochromatic  
16 VITA® shades

Variants  
white

### Opaque

35 % translucency  
flexural strength > 1,150 MPa  
suitable for a wide range of indications

16 VITA® shades and white



Variants  
monochromatic  
16 VITA® shades

Variants  
white

## Why does pritidenta offer so many different translucencies, shades and heights?

Each lab or milling center has its own specific requirements regarding result, price, translucency and area of application: priti®multidisc ZrO<sub>2</sub> offers the right solution for every need - Good to know you have a choice when you need it!